



HAL
open science

VISCOPLASTIC PROPERTIES AND TRIBOLOGICAL BEHAVIOR OF DIAMOND-LIKE CARBON FILMS USING NANOINDENTATION AND NANOSCRATCH TESTS

Viviane Turq, Julien Fontaine, Jean-Luc Loubet, Denis Mazuyer

► **To cite this version:**

Viviane Turq, Julien Fontaine, Jean-Luc Loubet, Denis Mazuyer. VISCOPLASTIC PROPERTIES AND TRIBOLOGICAL BEHAVIOR OF DIAMOND-LIKE CARBON FILMS USING NANOINDENTATION AND NANOSCRATCH TESTS. May 2005, pp.A-39. hal-00140293

HAL Id: hal-00140293

<https://hal.science/hal-00140293v1>

Submitted on 5 Apr 2007

HAL is a multi-disciplinary open access archive for the deposit and dissemination of scientific research documents, whether they are published or not. The documents may come from teaching and research institutions in France or abroad, or from public or private research centers.

L'archive ouverte pluridisciplinaire **HAL**, est destinée au dépôt et à la diffusion de documents scientifiques de niveau recherche, publiés ou non, émanant des établissements d'enseignement et de recherche français ou étrangers, des laboratoires publics ou privés.

VISCOPLASTIC PROPERTIES AND TRIBOLOGICAL BEHAVIOR OF DIAMOND-LIKE CARBON FILMS USING NANOINDENTATION AND NANOSCRATCH TESTS

V. Turq, J. Fontaine, J. L. Loubet, D. Mazuyer

Ecole Centrale de Lyon, Laboratoire de Tribologie et Dynamique des Systèmes, UMR CNRS 5513
69134 Ecully Cedex, France

TEL : 33-472-186-287, Email: Viviane.Turq@ec-lyon.fr

Introduction

Diamond-Like Carbon (DLC) films have been shown to demonstrate various tribological behaviors: in ultra-high vacuum (UHV), with either friction coefficients as low as 0.01 or less and very mild wear, or very high friction coefficients (>0.4) and drastic wear. These behaviors depend notably on gaseous environment, hydrogen content of the film [1], and on its viscoplastic properties [2,3]. A relation between superlow friction in UHV and viscoplasticity has indeed been established for a-C:H films and confirmed for a fluorinated sample (a-C:F:H). In this study, nanoindentation and nanoscratch tests were conducted in ambient air, using a nanoindentation apparatus, in order to evaluate tribological behaviors, as well as mechanical and viscoplastic properties of different amorphous carbon films.

Experimental

The samples were deposited on a Si (100) substrate by Plasma Enhanced Chemical Vapor Deposition (PECVD) process at different bias voltages, either from acetylene, cyclohexane precursors by d.c.-PECVD, or hexafluorobenzene mixed with hydrogen precursor by r.f.-PECVD for the fluorinated sample (a-C:F:H, noted FDLC). Details of the deposition process can be found in [4,5]. Thickness of the coating is $1\mu\text{m}$, except for the FDLC, which is $0.4\mu\text{m}$.

Nanoindentation and nanoscratch tests were carried out in ambient air, at room temperature, with a MTS NanoIndenter[®] XP apparatus. A spherical (radius $10\mu\text{m}$) and a Berkovich diamond indenter were used. Mechanical and viscoplastic properties were evaluated from nanoindentation tests in continuous stiffness mode, using the Berkovich diamond indenter, with a maximum load of 100mN . As the load P is applied exponentially as a function of time, the ratio between loading rate P' and load P is kept constant during indentation, and thus the strain rate $\dot{\epsilon}$ is also constant. Five different ratios P'/P , from $3 \cdot 10^{-3}$ up to $3 \cdot 10^{-1}\text{Hz}$, were used. Nanotribological evaluation of the samples was conducted from nanoscratch tests at ramping load (0.1 to 10mN , 3 passes) and at constant load (5mN , 10 passes) with spherical diamond indenter.

Results

The strain rate sensitivity of the materials is estimated and fitted by a Norton-Hoff law: $H = H_0 \cdot \dot{\epsilon}^x$ where H is the hardness, H_0 a constant, $\dot{\epsilon}$ the strain and x a constant called viscoplastic exponent (Table 1). Contrary to UHV, no evidence of correlation between friction coefficients in ambient air and viscoplasticity can be made. But even in this environment, some very low friction coefficient values, as low as 0.04 (FDLC),




Figure 1: Constant load scratch micrograph

with very mild wear have been evidenced (Figure 1). Hardness H_0 seems to be the key parameter: wear resistance in the air is improved with higher H_0 and friction coefficient decreases with H_0 . Note that H_0 is also roughly linked with the hydrogen content of the coating for the non fluorinated samples, as it has been shown in [2]. The number of passes seems also to lead to a decrease of friction coefficient.

Sample	H content (at. %)	H_0 (GPa)	x	μ ramping load	μ constant load	Wear
FDLC	5/18(F)	16	0.060	0.04-0.14	0.080	~ none
AC8	34	13	0.014	0.06-0.11	0.083	~ none
AC5	40	11	0.068	0.05-0.16	0.078	mild
CY6.5	42	6.8	0.028	0.07-0.13	0.083	mild
CY5	42	1.3	0.076	0.10-0.22	0.183	severe

Table 1: Summary of nanofriction tests results and viscoplastic properties

Conclusion

This study shows that in ambient air, wear resistance and frictional behavior of a-C:H and a-C:F:H samples is improved with hardness H_0 . In UHV, the achievement of super-low friction is linked with the viscoplastic character. Thus, intermediary coating, with high hardness and viscoplastic exponent, as a-C:F:H will demonstrate satisfactory tribological behavior both in ambient air and in UHV.

References

- [1] C. Donnet et al., *Tribo. Lett.*, 9 (2000) 137.
- [2] J. Fontaine et al., *Tribo. Lett.*, 17 (2004) 709.
- [3] J. Fontaine et al., *Thin Solid Films*, (2005) *in press*.
- [4] C. Donnet et al., *Surf. Coat. Tech.*, 94-95 (1997) 456.
- [5] C. Donnet et al., *Surf. Coat. Tech.*, 94-95 (1997) 531.