

Contact:

Martin.Obligado@univ-grenoble-alpes.fr

muriel.lagauzere@univ-grenoble-alpes.fr






Soufflerie Lespinard

Research manager: Martin Obligado Technical manager: Muriel Lagauzere


 The Lespinard wind tunnel is part of the large equipment available at LEGI

It is a low-turbulence closed return wind tunnel with a measurement section of 0.75 m^2 and 4 m long




- $\,\circ\,$ It can reach velocities up to 45m/s with a turbulence level below $0.\,1\%$
- It is compatible with static and active grids that can generate diverse types of turbulence

Some details...




- A 3D traverse system allows to displace a set of probes within all the extension of the measurement section
- A hot-wire anemometry system is available (streamline and DISA anemometers, compatibles with single and multiple wires)
- Velocity can also be measured/controlled with pitot tubes and a manometer Furness FCO560
- It can be used for two-phase flow studies (the motors are isolated from water droplets and humidity)
- Some of the experimental techniques that have been used are: high-speed imaging, particle imaging velocimetry (PIV), phase doppler interferometry (PDI), sonic anemometry, aerodynamic force sensors, among others

The active grid



- The active grid is
 composed by 16 bars (8
 horizontal and 8 vertical)
- Each bar is controlled

Laser safety



independently by a motor

Motors allow to control
 the velocity and direction
 of the blades

The active grid allows to produce bespoke turbulence: atmospheric boundary layer, high intensity homogeneous isotropic turbulence, unstationary turbulence, etc...

- All walls at the measurement section are transparent
- The area is protected by a leather cabin, allowing to use high power lasers for experiments