



**HAL**  
open science

## Optimization of deep rib high speed phase modulators on 300mm industrial Si-photonics platform

Stephane Monfray, Sébastien Cremer, Nathalie Vulliet, Emmanuel Dubois,  
Florian Domengie, Sebastien Jan, Françoise Baille, Frederic Boeuf

► **To cite this version:**

Stephane Monfray, Sébastien Cremer, Nathalie Vulliet, Emmanuel Dubois, Florian Domengie, et al.. Optimization of deep rib high speed phase modulators on 300mm industrial Si-photonics platform. SPIE Photonics Europe, Conference 11364 - Applications of Photonic Technology - Integrated Photonics Platforms: Fundamental Research, Manufacturing and Applications, Apr 2020, Strasbourg, France. 1136403, 8 p., 10.1117/12.2554725 . hal-03092725

**HAL Id: hal-03092725**

**<https://hal.science/hal-03092725>**

Submitted on 4 Jan 2021

**HAL** is a multi-disciplinary open access archive for the deposit and dissemination of scientific research documents, whether they are published or not. The documents may come from teaching and research institutions in France or abroad, or from public or private research centers.

L'archive ouverte pluridisciplinaire **HAL**, est destinée au dépôt et à la diffusion de documents scientifiques de niveau recherche, publiés ou non, émanant des établissements d'enseignement et de recherche français ou étrangers, des laboratoires publics ou privés.

# Optimization of Deep Rib High Speed Phase Modulators on 300mm Industrial Si-Photonics Platform

S.MONFRAY<sup>1</sup>, S.CREMER<sup>1</sup>, N.VUILLET<sup>1</sup>, E.DUBOIS<sup>2</sup>, F.DOMENGIE<sup>1</sup>, S.JAN<sup>1</sup>, F.BAILLE<sup>1</sup>, F.BŒUF<sup>1</sup>

<sup>1</sup>STMicroelectronics, 850 Rue Jean Monnet, Crolles, 38920, France,

<sup>2</sup>IEMN, Cité Scientifique, Avenue Poincaré, BP 60069, 59652 Villeneuve d'Ascq, France

[stephane.monfray@st.com](mailto:stephane.monfray@st.com)

**Abstract**— This paper highlights the optimization of Deep Rib High Speed Phase Modulators for 400G applications thanks to the optimal choice of structure and implants through a Design Of Experiment analysis, including the proposal of a new Deep Rib HSPM with Z-implants. Results show 1,6dB gain in OMA (Optical Modulation of Amplitude) at the same cutoff frequency ( $f_c = [2P_i * RC]^{-1}$ ) compared to the previous generation [1] with optimized vertical implants, and up to 2,15dB gain vs [1] with the new Z-implant Deep Rib device.

**Keywords**—*photonics, Deep Rib PN junction modulators*

## I. INTRODUCTION

Silicon photonics technology provides unreached data densities and integration level while taking benefits from low cost and industrial manufacturing infrastructure of CMOS electronics [1]. In this paper, O-band Silicon PN junction modulators have been designed and integrated. In order to improve light confinement in the core for maximizing the modal overlap with PN junction, we optimized a Deep Rib architecture. The purpose of this paper is to demonstrate the optimization of the modulator to obtain the best optical performances and speed with optimized implants and structure thanks to a DOE (Design Of Experiments) analysis, and to propose a new combination of well implants (named Z-implants) with the optimized Deep Rib geometry to reach OMA (Optical Modulation Amplitude) value as high as -2dBm with high cut-off frequency.

## II. DOE DEVICES INTEGRATION ON 300MM PHOTONICS PLATFORM

A Design Of Experiments (DOE) for Deep Rib modulators was tested on our 300mm Si-Photonics platform, including Ge Photodiodes, Si & SiN waveguides and transitions (see Fig.1) for CWDM circuits.





Fig.1: 300mm Si Photonic Platform including Si & SiN waveguides, adiabatic transition, Thick M4 Cu level and Deep Rib HSPM modulators. Integrated Ge PD is not shown on the picture.

The Design of Experiments (DOE) for Deep Rib modulators was first established with variations on the junction position  $X_j$

(from 20nm to 160nm), on the width of the modulator ( $W$  from 320 nm to 600nm) and on the distance  $d$  of access arms implants to the guide (from 100nm to 400nm) with different levels of doping (Process of reference Arm Doping  $x1$  and highly doped Arm Doping  $x20$ ), see figures 2a and 2b.



To extract the intrinsic cut-off frequency ( $f_c$ ) of the modulator PN junction, a so-called OPEN deembedding procedure has been applied to eliminate RC parasitics associated to the probing pads and interconnect layers from the topmost Metal4 to the inner Metal2 layers. This involves two distinct S-parameters measurements of the active device and of the passive OPEN structure, respectively. By subtracting the admittance of the OPEN from that of the modulator PN junction, the intrinsic RC product is subsequently easily determined to yield  $f_c$ . All RF measurements were performed with a reverse PN junction bias of 1.8V. The figure 3 shows that by reducing the distance to the waveguide of the Arm implants combined with a high dose ( $x20$  vs industrial reference [1],  $R$  can be largely reduced leading to high  $f_c$ .





Fig 3 shows the measured cutoff frequency in function of  $d$  distance, for two levels of Arm Doping ( $x1$  and  $x20$ ) vs previous industrial reference [1])

However, this optimization has to take into account the impact on optical performances (in particular losses) induced by the

doping modification. To explore this, we decided to monitor the OMA (Optical Modulation Amplitude) value for all structures of the DOE. OMA is defined as the difference between the optical power levels ( $P_{high}$  and  $P_{low}$ ) of the signal. The value of OMA is calculated based on the extracted HSPM parameters:  $\alpha$ =total device Losses (dB/mm), PS=device Phase Shift ( $^\circ$ /mm) and L=device length (mm).



We highlighted that by increasing by a factor 20 ( $N=1e19cm^{-3}$ ) the implant dose in the access arms down a distance to the waveguide  $d=250nm$ , the cutoff frequency could be highly improved (fig.3) without penalty on optical performances (fig. 4). For shorter distance, higher losses lead to OMA decrease.




Fig 4: impact of the Arm implant distance from the Si guide on the optical performances (OMA), for two levels of Arm doping (reference and x20).

### III. OPTIMIZED DEVICES INTEGRATION WITH VERTICAL PN IMPLANTS

In order to determine the best structure, we first performed TCAD simulations of all DOE structures to evaluate the access resistance, while other parameters (capacitances, losses, phase-shift) were measured on the fabricated devices. Thanks to the DOE analysis, we determined that the best optical performances was obtained for  $X_j=60nm$  and a width of  $400nm$ . Experimentally, the closest measured device had a width of  $370nm$  and was highlighted as the best point of our OMA vs  $fc$  ( $=1/2PiRC$ ) figure of merit (fig.5).




Fig 5: DOE results for different geometrical and implants parameters. Best structure for compromise OMA vs cut-off frequency is identified. L=2,4mm.

The same DOE was then measured with the RF structures (fig. 6) to extract the exact  $fc$  with a reverse bias of  $1,8V$ , and confirmed the best performances for our identified experimental geometry ( $W=370nm$ ,  $X_j=60nm$ ,  $d_{Arm}$  implant distance= $250nm$ ) with the highest Arm implant dose (x20 vs the previous platform).




Fig 6: Confirmation of best geometry confirmed with cut-off frequencies measured at  $1,8V$  reverse bias on dedicated RF structures. L=2,4mm.

Then we optimized the value of the Waveguide (Wells) implants by increasing sequentially the dose of Pwell and Nwell vs the reference. The figure 7 show that we improved OMA by increasing both values by a 1,5 factor.




Fig.7: (left) Impact of Si guide Pwell implant increase for a given Nwell value and (right) Impact of Si guide Nwell implant increase for the best Nwell implant. OMA is optimum for the highest values. L=2,4mm.

Finally, compared to our previous industrial platform (Rib modulators in [1]) we can see on figure 8 that the optimized Deep Rib structure improves the OMA by  $1,6dB$  with an improved cut off frequency ( $1/2PiRC$ ).






Fig 8: Impact of well implants increase for the best HSPM geometry. OMA is improved from  $-3,25dBm$  to  $-2,85dBm$  on the Deep Rib structure. L=2,4mm. Compared to [1], OMA is improved by  $1,6dB$ .

The figure 9 provides OMA vs L characteristic for the best device.



The figure 13 provides OMA vs L characteristic for the best device.



#### IV. NEW DEEP RIB DEVICES INTEGRATION WITH Z IMPLANTS

We propose in this section the combination of our best Deep-Rib geometry with Z-implants (combination of depths of vertical N-well implants) to improve the coverage between the highly confined mode in the Deep-Rib structure and the depletion zone of the PN junction (fig.10).








Fig 10: Proposal of new Z-implant structure on Deep-Rib best architecture. Z-implants are optimized to ensure a better electrostatic coverage of the optical mode (left) vs the classical vertical implants (right).

The same DOE was analyzed with these Z-implants and the best geometry was the same as previously identified, but with  $X_j=140\text{nm}$  to ensure the best overlap with the junction. Fig.11 & 12 shows the optical performances of the structure and compare it with the previous points. One can see that this approach improves OMA by 2,15dB compared to our previous platform, by assuming a slight decrease of the cut-off frequency.



Finally, we compared the 3 structures: Rib modulator from [1], the optimized vertical PN Deep-Rib modulator (from fig.8) and the Deep-Rib modulator with Z-implants. OMA (calculated based on experimental data) in function of device length graphs and  $V_{\text{Pi}}*L_{\text{Pi}}$  highlight the improvement proposed by those structures compared to the reference platform.



#### V. CONCLUSION

This paper shows optimized deep Rib modulators for 400G and above applications. DOE integration allowed us to define the optimal structure and implants to guaranty high speed (high cutoff frequency) coupled with high optical performances, to propose highly performant silicon PN junction modulator with OMA improved by 1,6dB and up to 2,15dB compared to the industrial state-of-the-art. The best Deep Rib geometry with Z-implants has OMA (Optical Modulation Amplitude) value as high as -2dBm ( $L=3\text{mm}$ ) with 54GHz@0V cut-off frequency.

This work was partially supported by H2020 project N° 688516 COSMICC and project IRT Nanoelec.

[1] F.Boeuf et al., "Silicon Photonics R&D and Manufacturing on 300-mm Wafer Platform" JOURNAL OF LIGHTWAVE TECHNOLOGY, VOL. 34, NO. 2, JANUARY 15, 2016

[2] E. Temporiti et al. Solid State Elec. 2016,